

AAM7F53Z11 Cut Sheet



AutomationDirect IEC limit switch, side rotary adjustable metal lever with 18mm metal roller, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, zinc alloy, (1) 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AAM7F53Z11>

Technical Specifications

Brand	AutomationDirect
Item	Limit switch
Switch Type	IEC
Actuator Type	Side rotary adjustable metal lever with 18mm metal roller
Head Type	90-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action

Reset	No
Body Width	30.3mm
Mounting Hole Spacing	20-22mm
Material	Zinc alloy
IP Rating	IP66
Operating Temperature	-10 to 70 deg C
Connection	(1) 5-pin M12 quick-disconnect

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AAM7F53Z11.pdf>
See store item page for other formats.