AAP7T35Z11 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

AchieVe IEC limit switch, one-way horizontal lever with polyamide roller, 90-degree adjustable head, (1) N.O./(1) N.C. contact(s), snap action, 20–22mm hole spacing, plastic, (1) 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/AAP7T35Z11

Technical Specifications

Brand	AchieVe
Item	Limit switch
Switch Type	IEC
Actuator Type	One-way horizontal lever with polyamide roller
Head Type	90-degree adjustable
Contact Type	(1) N.O./(1) N.C.
Action	Snap action
Body Width	30.3mm
Mounting Hole Spacing	20–22mm
Material	Plastic
IP Rating	IP65
Operating Temperature	-25 to +70 °C
Connection	(1) 5-pin M12 quick-disconnect

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/AAP7T35Z11.pdf
See store item page for other formats.