

ABM1E42Z11 Cut Sheet



AutomationDirect IEC limit switch, side rotary lever with stainless steel roller, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 30mm hole spacing, aluminum, (1) PG13.5 cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ABM1E42Z11>

Technical Specifications

Brand	AutomationDirect
Item	Limit switch
Switch Type	IEC
Actuator Type	Side rotary lever with stainless steel roller
Head Type	90-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No
Body Width	40mm
Mounting Hole Spacing	30mm
Material	Aluminum
IP Rating	IP66
Operating Temperature	-10 to 70 deg C
Connection	(1) PG13.5 cable entry

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document