

ABM5E71Z11 Cut Sheet



AutomationDirect IEC limit switch, side rotary stainless steel rod, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 40mm hole spacing, aluminum, (3) PG13.5 cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ABM5E71Z11>

Technical Specifications

Brand	AutomationDirect
Item	Limit switch
Switch Type	IEC
Actuator Type	Side rotary stainless steel rod
Head Type	90-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No
Body Width	66mm
Mounting Hole Spacing	40mm
Material	Aluminum
IP Rating	IP66
Operating Temperature	-10 to 70 deg C
Connection	(3) PG13.5 cable entries

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document