

ABN12242508 Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 24 x 25 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ABN12242508>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
NEMA Rating	12/13
Disconnect Mounting	Right flange
Nominal Enclosure Height	24in
Nominal Enclosure Width	25.38in
Nominal Enclosure Depth	8.85in
Mounting	Wall
Integral Mounting Feet	Yes
Material	Carbon steel

Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Padlockable	No
Keylocking	No
Subpanel	Purchase subpanel separately
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, operating handle, and door hardware from Allen-Bradley

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ABN12242508.pdf>
See store item page for other formats.