

ABN12363108 Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 36 x 31 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ABN12363108>

Technical Specifications

Brand	Wiegmann	Color	ANSI 61 gray
Item	Disconnect enclosure	Finish	Powder coat
Slope Top	No	Cover Type	Single-door
NEMA Rating	12/13	Hinge Type	Continuous hinge
Disconnect Mounting	Right flange	Number of Hinges Per Door	1
Nominal Enclosure Height	36in	Padlockable	No
Nominal Enclosure Width	31.38in	Keylocking	No
Nominal Enclosure Depth	8.85in	Subpanel	Purchase subpanel separately
Mounting	Wall	Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, operating handle, and door hardware from Allen-Bradley
Integral Mounting Feet	Yes		
Material	Carbon steel		

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ABN12363108.pdf>
See store item page for other formats.