

# ABN12483710 Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 48 x 37 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ABN12483710>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>NEMA Rating</b>	12/13
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Height</b>	48in
<b>Nominal Enclosure Width</b>	37.38in
<b>Nominal Enclosure Depth</b>	10.85in
<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	Yes
<b>Material</b>	Carbon steel

<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Single-door
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Padlockable</b>	No
<b>Keylocking</b>	No
<b>Subpanel</b>	Purchase subpanel separately
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, operating handle, and door hardware from Allen-Bradley

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ABN12483710.pdf>  
See store item page for other formats.