

ACG-ET2 Cut Sheet



IronHorse ACG series communication module, EtherNet/IP and Modbus TCP, 2 ports, (2) Ethernet (RJ45) and (1) RS-485 (RJ45) port(s). For use with IronHorse ACG series AC drives. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACG-ET2>

Technical Specifications

Brand	IronHorse
Item	Communication module
Series	ACG
Number of Ports	2
Buffered Ports	No
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (2) Ethernet (RJ45)• (1) RS-485 (RJ45)
Port Protocol(s)	<ul style="list-style-type: none">• EtherNet/IP Server• Modbus TCP Slave
Port Speed(s)	10/100 Mbps
For Use With	IronHorse ACG series AC drives
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ACG-ET2.pdf>
See store item page for other formats.