

ACL1 Cut Sheet



AcuAMP AC current indicator, fixed core, 0.5-100A sensing range, 0.5A non-adjustable trip point.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACL1>

Technical Specifications

Brand	AcuAMP
Item	Current indicator
Voltage Type	AC
Body Type	Fixed core
Sensing Range	0.5-100A
True RMS	No
Trip Point	0.5A non-adjustable
Operating Voltage	Self powered
UL Rating	UL 508 listed

Agency Approvals

UL Listed File #	E222847
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ACL1.pdf>
See store item page for other formats.