

ACN-ETH Cut Sheet



IronHorse ACN series communication module, EtherNet/IP and Modbus TCP, 1 port, (1) Ethernet (RJ45) and (1) RS-232 (RJ45) port(s). For use with IronHorse ACN series drives. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACN-ETH>

Technical Specifications

Brand	IronHorse
Item	Communication module
Series	ACN
Number of Ports	1
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) Ethernet (RJ45)• (1) RS-232 (RJ45)
Port Protocol(s)	<ul style="list-style-type: none">• EtherNet/IP Server• Modbus TCP Slave
Port Speed(s)	10/100 Mbps
For Use With	IronHorse ACN series drives
Includes	Mounting hardware
Additional Information	RS-232 (RJ45) port for connection to ACN-LCD remote keypad or PC only

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document