

ACSN100-AE-F Cut Sheet



AcuAMP AC current switch, fixed core, 0-100A sensing range, 0.5A non-adjustable trip point, solid state switch, N.O. output, 0.15A @ 120 VAC/VDC output rating.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACSN100-AE-F>

Technical Specifications

Brand	AcuAMP
Item	AC Current switch
Body Type	Fixed core
Sensing Range	0-100A
True RMS	No
Trip Point	0.5A non-adjustable
Output	Solid state switch, N.O.
Output Rating	0.15A @ 120 VAC/VDC
Operating Voltage	Self powered
Mounting	Panel or optional 35mm DIN rail
Electrical Connection	24-in lead wires
UL Rating	UL 508 listed

Agency Approvals

UL Listed File #	E222847
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document