

ACSN250-AE-S Cut Sheet



AcuAMP AC current switch, split core, 0-250A sensing range, 1.25A non-adjustable trip point, solid state switch, N.O. output, 0.15A @ 240 VAC/VDC output rating.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACSN250-AE-S>

Technical Specifications

| | |
|------------------------------|---------------------------------|
| Brand | AcuAMP |
| Item | AC Current switch |
| Body Type | Split core |
| Sensing Range | 0-250A |
| True RMS | No |
| Trip Point | 1.25A non-adjustable |
| Output | Solid state switch, N.O. |
| Output Rating | 0.15A @ 240 VAC/VDC |
| Operating Voltage | Self powered |
| Mounting | Panel or optional 35mm DIN rail |
| Electrical Connection | Screw terminals |
| UL Rating | UL 508 listed |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E222847 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |