

ACT005-42L-F Cut Sheet



AcuAMP AC current transducer, 1-phase, fixed core, 0-2 or 0-5A selectable sensing range, 4-20mA output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACT005-42L-F>

Technical Specifications

| | |
|-----------------------|---------------------------------|
| Brand | AcuAMP |
| Item | AC Current transducer |
| Number of Phases | 1 |
| Body Type | Fixed core |
| Sensing Range | 0-2 or 0-5A selectable |
| True RMS | No |
| Output | 4-20mA |
| Operating Voltage | 24 VDC |
| Mounting | Panel or optional 35mm DIN rail |
| Electrical Connection | Screw terminals |
| UL Rating | UL 508 listed |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E222847 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |