

ACTR1000-42L-S Cut Sheet



AcuAMP AC current transducer, flexible split core, 0-1000A sensing range, True RMS, 4-20mA output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ACTR1000-42L-S>

Technical Specifications

Brand	AcuAMP
Item	AC Current transducer
Body Type	Flexible split core
Sensing Range	0-1000A
True RMS	Yes
Output	4-20mA
Operating Voltage	24 VDC
Mounting	35mm DIN rail
Electrical Connection	Screw terminals
UL Rating	UL 508 listed

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document