

AD-HSSR810-AC-28 Cut Sheet



AutomationDirect solid state relay, 35mm DIN rail mount, finger-safe, 90-280 VAC input voltage, SPST, (1) N.O. SCR, 10A contact rating, 24-280 VAC load voltage, zero cross, screw terminal(s), LED indicator(s), hazardous location certified.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD-HSSR810-AC-28>

Technical Specifications

| | |
|----------------------------|------------------------------|
| Brand | AutomationDirect |
| Item | Relay |
| Relay Type | Solid state |
| Mounting | 35mm DIN rail |
| Relay Housing Type | Finger-safe |
| Input Voltage | 90-280 VAC |
| Relay Configuration | SPST |
| Output Type | (1) N.O. SCR |
| Load Voltage | 24-280 VAC |
| Contact Rating | 10A |
| Switching Type | Zero cross |
| Connector Type | Screw terminal(s) |
| Indicator | LED |
| Application | Hazardous location certified |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E344125 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |