

AD-PR40-2A-24D Cut Sheet



AutomationDirect power relay, panel mount, open, 24 VDC coil voltage, DPST, (2) N.O., 40A contact rating, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD-PR40-2A-24D>

Technical Specifications

Brand	AutomationDirect
Item	Relay
Relay Type	Power
Mounting	Panel
Relay Housing Type	Open
Coil Voltage	24 VDC
Relay Configuration	DPST
Output Type	(2) N.O.
Contact Rating	40A
Connector Type	Screw terminal(s)

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	244610
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document