

AD-PR40-2C-24A Cut Sheet



AutomationDirect power relay, panel mount, open, 24 VAC coil voltage, DPDT, (2) N.O., (2) N.C., 40A contact rating, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD-PR40-2C-24A>

Technical Specifications

| | |
|----------------------------|--------------------|
| Brand | AutomationDirect |
| Item | Relay |
| Relay Type | Power |
| Mounting | Panel |
| Relay Housing Type | Open |
| Coil Voltage | 24 VAC |
| Relay Configuration | DPDT |
| Output Type | (2) N.O., (2) N.C. |
| Contact Rating | 40A |
| Connector Type | Screw terminal(s) |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E191059 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 244610 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |