

# AD-SSR610-DC-480A Cut Sheet



AutomationDirect solid state relay, panel mount, finger-safe hockey puck, 3-32 VDC input voltage, SPST, (1) N.O. SCR, 10A contact rating, 48-480 VAC load voltage, zero cross, screw terminal(s), LED indicator(s). Thermal mounting pad included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD-SSR610-DC-480A>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Relay
<b>Relay Type</b>	Solid state
<b>Mounting</b>	Panel
<b>Relay Housing Type</b>	Finger-safe hockey puck
<b>Input Voltage</b>	3-32 VDC
<b>Relay Configuration</b>	SPST
<b>Output Type</b>	(1) N.O. SCR
<b>Load Voltage</b>	48-480 VAC
<b>Contact Rating</b>	10A
<b>Switching Type</b>	Zero cross
<b>Connector Type</b>	Screw terminal(s)
<b>Indicator</b>	LED
<b>Includes</b>	Thermal mounting pad

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E222847
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	244610
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AD-SSR610-DC-480A.pdf>  
See store item page for other formats.