

AD-SSR6T25-DC-280A Cut Sheet



AutomationDirect solid state relay, panel mount, finger-safe hockey puck, 3-32 VDC input voltage, SPST, (1) N.O. TRIAC, 25A contact rating, 24-280 VAC load voltage, zero cross, screw terminal(s), LED indicator(s). Thermal mounting pad included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD-SSR6T25-DC-280A>

Technical Specifications

| | |
|---------------------|-------------------------|
| Brand | AutomationDirect |
| Item | Relay |
| Relay Type | Solid state |
| Mounting | Panel |
| Relay Housing Type | Finger-safe hockey puck |
| Input Voltage | 3-32 VDC |
| Relay Configuration | SPST |
| Output Type | (1) N.O. TRIAC |
| Load Voltage | 24-280 VAC |
| Contact Rating | 25A |
| Switching Type | Zero cross |
| Connector Type | Screw terminal(s) |
| Indicator | LED |
| Includes | Thermal mounting pad |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E222847 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 244610 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AD-SSR6T25-DC-280A.pdf>
See store item page for other formats.