


AD03007 Cut Sheet



Continental hydraulic solenoid valve, D03, 4-port (4-way), 3-position, center float, double solenoid, cast iron body, momentary manual override, 23.2 GPM, 24 VDC, 31W, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD03007>

Technical Specifications

Brand	Continental	Manual Override Type	Momentary
Item	Valve	Flow Capacity	23.2 GPM
Working Fluid	Petroleum based hydraulic fluid	Maximum Operating Pressure	5000 psi
Valve Type	Solenoid directional control	Minimum Operating Pressure	0 psi
Port Quantity	4-port (4-way)	Working Fluid Temperature	-4 to +176 °F
Number Of Positions	3	Operating Voltage	24 VDC
Valve Configuration	Center float	Power Rating	31W
Action	Double solenoid	Electrical Connection	18mm DIN style wiring plug
Body Material	Cast iron	Form Factor	D03
Seal Material	Viton	Includes	O-rings and mounting hardware
Mounting	Subplate or manifold	Manufacturer Part Number	VS6M-3F-G-D24WK1

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AD03007.pdf>
See store item page for other formats.