

AD03013 Cut Sheet



Continental hydraulic solenoid valve, D03, 4-port (4-way), 3-position, center closed, double solenoid, cast iron body, momentary manual override, 26.4 GPM, 120 VAC, 22 VA, conduit box.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD03013>

Technical Specifications

Brand	Continental
Item	Valve
Working Fluid	Petroleum based hydraulic fluid
Valve Type	Solenoid directional control
Port Quantity	4-port (4-way)
Number Of Positions	3
Valve Configuration	Center closed
Action	Double solenoid
Body Material	Cast iron
Seal Material	Viton
Mounting	Subplate or manifold

Manual Override Type	Momentary
Flow Capacity	26.4 GPM
Maximum Operating Pressure	5000 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-4 to +176 °F
Operating Voltage	120 VAC
Power Rating	22 VA
Electrical Connection	Conduit box
Form Factor	D03
Includes	O-rings and mounting hardware
Manufacturer Part Number	VSD03M-3A-GB-60L

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AD03013.pdf>
See store item page for other formats.