

# AD03017 Cut Sheet



Continental hydraulic manual valve, 4-port (4-way), 3-position, center closed, 90 deg hand lever, spring return to center from right or left, 20 GPM, subplate or manifold mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD03017>

## Technical Specifications

<b>Brand</b>	Continental
<b>Item</b>	Valve
<b>Working Fluid</b>	Petroleum based hydraulic fluid
<b>Valve Type</b>	Manual directional control
<b>Port Quantity</b>	4-port (4-way)
<b>Number Of Positions</b>	3
<b>Valve Configuration</b>	Center closed
<b>Operator Type</b>	90 deg hand lever
<b>Action</b>	Spring return to center from right or left
<b>Body Material</b>	Cast iron

<b>Seal Material</b>	Viton
<b>Mounting</b>	Subplate or manifold
<b>Flow Capacity</b>	20 GPM
<b>Maximum Operating Pressure</b>	5000 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Working Fluid Temperature</b>	-4 to +180 °F
<b>Form Factor</b>	D03
<b>Includes</b>	O-rings and mounting hardware
<b>Manufacturer Part Number</b>	VMD03M-3A-G-10-B

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/AD03017.pdf>  
See store item page for other formats.