

AD03018 Cut Sheet



Continental hydraulic manual valve, 4-port (4-way), 3-position, center float, 90 deg hand lever, spring return to center from right or left, 20 GPM, subplate or manifold mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AD03018>

Technical Specifications

Brand	Continental
Item	Valve
Working Fluid	Petroleum based hydraulic fluid
Valve Type	Manual directional control
Port Quantity	4-port (4-way)
Number Of Positions	3
Valve Configuration	Center float
Operator Type	90 deg hand lever
Action	Spring return to center from right or left
Body Material	Cast iron

Seal Material	Viton
Mounting	Subplate or manifold
Flow Capacity	20 GPM
Maximum Operating Pressure	5000 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-4 to +180 °F
Form Factor	D03
Includes	O-rings and mounting hardware
Manufacturer Part Number	VMD03M-3F-G-10-B

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AD03018.pdf>
See store item page for other formats.