

ADM100-HP Cut Sheet



Trumeter ADM100 standard graphical multi-function meter, RMS AC/DC Current, RMS AC/DC Voltage or frequency input, 3in positive backlit LCD configurable to white, green, red, (2) discrete or current outputs, 100-240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADM100-HP>

Technical Specifications

Brand	Trumeter
Item	Graphical multi-function meter
Series	ADM100
Application	Standard
Display Type	3in positive backlit LCD configurable to white, green, red
Input Current Signal Range	5A
Input Voltage Signal Range	0-600 VAC/VDC
Input Frequency Signal Range	2-400 Hz
Discrete Output Type	Open collector (34 VDC/0.5A)
Output Current Signal Range	4-20 mA

Operating Voltage	100-240 VAC
Accuracy	1%
NEMA Rating	4/12
IP Rating	IP65
Mounting	Panel
Mounting Hole Size	68 x 68mm (2.68 x 2.68in)
Additional Information	Configurable using the free downloadable utility software. User customizable display parameters are static or based on alarm threshold: scaling, blinking, color, intensity, 4 digit alphanumeric message

Agency Approvals

UL Listed File #	E469787
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ADM100-HP.pdf>
See store item page for other formats.