

ADM100P-LP Cut Sheet



Trumeter ADM100 standard graphical process meter, current or voltage input, 3in positive backlit LCD configurable to white, green, red, (2) discrete or current outputs, 12-24 VAC/VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADM100P-LP>

Technical Specifications

Brand	Trumeter
Item	Graphical process meter
Series	ADM100
Application	Standard
Display Type	3in positive backlit LCD configurable to white, green, red
Input Current Signal Range	0-50 mA
Input Voltage Signal Range	0 to +/-10 VDC
Discrete Output Type	Open collector (34 VDC/0.5A)
Output Current Signal Range	4-20 mA

Operating Voltage	12-24 VAC/VDC
Accuracy	0.1% voltage, 0.01% current
NEMA Rating	4
IP Rating	IP65
Mounting	Panel
Mounting Hole Size	68 x 68mm (2.68 x 2.68in)
Additional Information	Configurable using the free downloadable utility software. User customizable display parameters are static or based on alarm threshold: scaling, blinking, color, intensity, 4 digit alphanumeric message

Agency Approvals

UL Listed File #	E469787
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ADM100P-LP.pdf>
See store item page for other formats.