

ADM100T-LN Cut Sheet



Trumeter ADM100 standard graphical temperature meter, thermocouple input, 3in negative backlit LCD configurable to white, green, red, (2) discrete or current outputs, 12-24 VAC/VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADM100T-LN>

Technical Specifications

Brand	Trumeter
Item	Graphical temperature meter
Series	ADM100
Application	Standard
Display Type	3in negative backlit LCD configurable to white, green, red
Input Thermocouple Signal Type	B, E, J, K, N, R, S, T
Discrete Output Type	Open collector (34 VDC/0.5A)
Output Current Signal Range	4-20 mA

Operating Voltage	12-24 VAC/VDC
Accuracy	0.25%
NEMA Rating	4
IP Rating	IP65
Mounting	Panel
Mounting Hole Size	68 x 68mm (2.68 x 2.68in)
Additional Information	Configurable using the free downloadable utility software. User customizable display parameters are static or based on alarm threshold: scaling, blinking, color, intensity, 4 digit alphanumeric message

Agency Approvals

UL Listed File #	E469787
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ADM100T-LN.pdf>
See store item page for other formats.