

ADP2T71Z11 Cut Sheet



AchieVe IEC limit switch, side rotary adjustable 3mm stainless steel rod, 90-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm or 40-42mm hole spacing, plastic, (2) PG11 cable entries with (1) 1/2in NPT adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADP2T71Z11>

Technical Specifications

| | |
|------------------------------|---|
| Brand | AchieVe |
| Item | Limit switch |
| Switch Type | IEC |
| Actuator Type | Side rotary adjustable 3mm stainless steel rod |
| Head Type | 90-degree adjustable |
| Contact Type | (1) N.O./ (1) N.C. |
| Action | Snap action |
| Reset | No |
| Body Width | 50mm |
| Mounting Hole Spacing | 20-22mm or 40-42mm |
| Material | Plastic |
| IP Rating | IP66 |
| Operating Temperature | -25 to 70 deg C |
| Connection | (2) PG11 cable entries with (1) 1/2in NPT adapter |
| Halogen Free | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | NKCR.E191072 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |