

ADPH24010 Cut Sheet



Eaton Aegis series powerline filter, 240 VAC, 1-phase, 10A, 35mm DIN rail mount, EMI/RFI filtering, LED indication, UL Type 2, SPDT alarm, screw terminals, 5kA SCCR.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADPH24010>

Technical Specifications

Brand	Eaton
Item	Powerline filter
Series	Aegis
Voltage Rating	240 VAC
Number of Phases	1
Amperage Rating	10A
Mounting	35mm DIN rail
Filtering	EMI/RFI
Indicating Type	LED indication
Surge Protection Type	UL Type 2
Output Type	SPDT alarm
Connection	Screw terminals
SCCR Rating	5kA SCCR
Additional Information	SPDT rated 8A at 250 VAC / 30 VDC
UL Rating	UL 1283, UL 1449 rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	E316410
UL Hazardous File #	None
CE	None
CSA File #	163545
RoHS Status	No
EU REACH	View EU REACH document