

# ADPH24015 Cut Sheet



Eaton Aegis series powerline filter, 240 VAC, 1-phase, 15A, 35mm DIN rail mount, EMI/RFI filtering, LED indication, UL Type 2, SPDT alarm, screw terminals, 5kA SCCR.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ADPH24015>

## Technical Specifications

<b>Brand</b>	Eaton
<b>Item</b>	Powerline filter
<b>Series</b>	Aegis
<b>Voltage Rating</b>	240 VAC
<b>Number of Phases</b>	1
<b>Amperage Rating</b>	15A
<b>Mounting</b>	35mm DIN rail
<b>Filtering</b>	EMI/RFI
<b>Indicating Type</b>	LED indication
<b>Surge Protection Type</b>	UL Type 2
<b>Output Type</b>	SPDT alarm
<b>Connection</b>	Screw terminals
<b>SCCR Rating</b>	5kA SCCR
<b>Additional Information</b>	SPDT rated 8A at 250 VAC / 30 VDC
<b>UL Rating</b>	UL 1283, UL 1449 rated

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E316410
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	163545
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>