

AEM2G1501Z11M Cut Sheet



AutomationDirect compact limit switch, metal plunger with nylon cross roller, (1) N.O./(1) N.C. contact(s), snap action, 25mm hole spacing, zinc alloy, 5-pin M12 quick-disconnect, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEM2G1501Z11M>

Technical Specifications

Brand	AutomationDirect
Item	Limit switch
Switch Type	Compact
Actuator Type	Metal plunger with nylon cross roller
Contact Type	(1) N.O./(1) N.C.
Action	Snap action
Reset	No
Body Width	35mm
Mounting Hole Spacing	25mm
Material	Zinc alloy
IP Rating	IP67
Operating Temperature	-25 to 70 deg C
Connection	5-pin M12 quick-disconnect
Cable Exit	Bottom

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document