

AEM2G16Z11-3 Cut Sheet



AutomationDirect compact limit switch, metal plunger with dust cap, (1) N.O./ (1) N.C. contact(s), snap action, 25mm hole spacing, zinc alloy, pigtail, 9.8ft/3m cable length, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEM2G16Z11-3>

Technical Specifications

| | |
|------------------------------|-----------------------------|
| Brand | AutomationDirect |
| Item | Limit switch |
| Switch Type | Compact |
| Actuator Type | Metal plunger with dust cap |
| Contact Type | (1) N.O./ (1) N.C. |
| Action | Snap action |
| Reset | No |
| Body Width | 35mm |
| Mounting Hole Spacing | 25mm |
| Material | Zinc alloy |
| IP Rating | IP67 |
| Operating Temperature | -25 to 70 deg C |
| Connection | Pigtail |
| Conductor Size | 18 AWG |
| Jacket Material | PVC |
| Cable Length | 9.8ft/3m |
| Cable Exit | Bottom |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E191072 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |