

AEM2G2201Z11-3R Cut Sheet



AutomationDirect compact limit switch, metal plunger with metal roller and fixing nuts, (1) N.O./ (1) N.C. contact(s), snap action, 25mm hole spacing, zinc alloy, pigtail, 9.8ft/3m cable length, right exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEM2G2201Z11-3R>

Technical Specifications

Brand	AutomationDirect
Item	Limit switch
Switch Type	Compact
Actuator Type	Metal plunger with metal roller and fixing nuts
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No
Body Width	35mm
Mounting Hole Spacing	25mm

Material	Zinc alloy
IP Rating	IP67
Operating Temperature	-25 to 70 deg C
Connection	Pigtail
Conductor Size	18 AWG
Jacket Material	PVC
Cable Length	9.8ft/3m
Cable Exit	Right

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AEM2G2201Z11-3R.pdf>
See store item page for other formats.