

# AEM2G5120Z22-3 Cut Sheet



AchieVe compact limit switch, side rotary adjustable lever with 18mm nylon roller, (2) N.O./ (2) N.C. contact(s), snap action, 25mm hole spacing, zinc alloy, pigtail, 9.8ft/3m cable length, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEM2G5120Z22-3>

## Technical Specifications

Brand	AchieVe
Item	Limit switch
Switch Type	Compact
Actuator Type	Side rotary adjustable lever with 18mm nylon roller
Contact Type	(2) N.O./ (2) N.C.
Action	Snap action
Reset	No
Body Width	35mm
Mounting Hole Spacing	25mm

Material	Zinc alloy
IP Rating	IP67
Operating Temperature	-25 to 70 deg C
Connection	Pigtail
Conductor Size	20 AWG
Jacket Material	PVC
Halogen Free	No
Cable Length	9.8ft/3m
Cable Exit	Bottom

## Agency Approvals

UL Listed File #	NKCR.E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/AEM2G5120Z22-3.pdf>  
See store item page for other formats.