

# AEM2G7120Z11MR Cut Sheet



AutomationDirect compact limit switch, side rotary adjustable 3mm stainless steel rod, (1) N.O./(1) N.C. contact(s), snap action, 25mm hole spacing, zinc alloy, (1) 5-pin M12 quick-disconnect, right exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEM2G7120Z11MR>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Limit switch
<b>Switch Type</b>	Compact
<b>Actuator Type</b>	Side rotary adjustable 3mm stainless steel rod
<b>Contact Type</b>	(1) N.O./(1) N.C.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	35mm
<b>Mounting Hole Spacing</b>	25mm
<b>Material</b>	Zinc alloy
<b>IP Rating</b>	IP67
<b>Operating Temperature</b>	-25 to 70 deg C
<b>Connection</b>	(1) 5-pin M12 quick-disconnect
<b>Cable Exit</b>	Right

## Agency Approvals

<b>UL Listed File #</b>	E191072
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AEM2G7120Z11MR.pdf>  
See store item page for other formats.