

AEP2G22Z22-1 Cut Sheet



AchieVe compact limit switch, metal plunger with metal roller and fixing nuts, (2) N.O./ (2) N.C. contact(s), snap action, 25mm hole spacing, plastic, pigtail, 3.2ft/1m cable length, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEP2G22Z22-1>

Technical Specifications

Brand	AchieVe
Item	Limit switch
Switch Type	Compact
Actuator Type	Metal plunger with metal roller and fixing nuts
Contact Type	(2) N.O./ (2) N.C.
Action	Snap action
Reset	No
Body Width	35mm
Mounting Hole Spacing	25mm

Material	Plastic
IP Rating	IP67
Operating Temperature	-25 to 70 deg C
Connection	Pigtail
Conductor Size	20 AWG
Jacket Material	PVC
Halogen Free	No
Cable Length	3.2ft/1m
Cable Exit	Bottom

Agency Approvals

UL Listed File #	NKCR.E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AEP2G22Z22-1.pdf>
See store item page for other formats.