

AEP2G42Z11-1 Cut Sheet



AutomationDirect compact limit switch, side rotary lever with 14mm metal roller, (1) N.O./(1) N.C. contact(s), snap action, 25mm hole spacing, plastic, pigtail, 3.2ft/1m cable length, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AEP2G42Z11-1>

Technical Specifications

Brand	AutomationDirect
Item	Limit switch
Switch Type	Compact
Actuator Type	Side rotary lever with 14mm metal roller
Contact Type	(1) N.O./(1) N.C.
Action	Snap action
Reset	No
Body Width	35mm
Mounting Hole Spacing	25mm
Material	Plastic
IP Rating	IP67
Operating Temperature	-25 to 70 deg C
Connection	Pigtail
Conductor Size	18 AWG
Jacket Material	PVC
Cable Length	3.2ft/1m
Cable Exit	Bottom

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document