

AF16JR-7AC2A Cut Sheet



Fuji Electric selector switch, IP65, 19mm, 3-position, spring return to center from right, maintained left, key removable left position, DPDT contact(s), plastic base, plastic bezel, Operator: silver, key, 22mm, round, metal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AF16JR-7AC2A>

Technical Specifications

Brand	Fuji Electric
Item	Selector switch
Barrel Size	19mm
IP Rating	IP65
Number Of Positions	3
Action	Spring return to center from right, maintained left
Key Removable Position	Key removable left position
Contact Type	DPDT
Base Material	Plastic
Bezel Material	Plastic
Operator Color	Silver
Operator Type	Key
Operator Size	22mm
Operator Shape	Round
Operator Material	Metal
Connection	2.8mm x 0.5mm female quick-disconnect

Agency Approvals

UL Listed File #	None
UL Recognized File #	E44592
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document