

# AF16PR-7C2B Cut Sheet



Fuji Electric selector switch, IP65, 19mm, 3-position, spring return to center from right, maintained left, DPDT contact(s), plastic base, plastic bezel, Operator: black, knob, 22mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AF16PR-7C2B>

## Technical Specifications

Brand	Fuji Electric
Item	Selector switch
Barrel Size	19mm
IP Rating	IP65
Number Of Positions	3
Action	Spring return to center from right, maintained left
Contact Type	DPDT
Base Material	Plastic

Bezel Material	Plastic
Operator Color	Black
Operator Type	Knob
Operator Size	22mm
Operator Shape	Round
Operator Material	Plastic
Connection	2.8mm x 0.5mm female quick-disconnect

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E44592
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/AF16PR-7C2B.pdf>  
See store item page for other formats.