

AFEPMKR4FR3-024E Cut Sheet



Comepi safety switch, tongue (key) interlock uniquely coded RFID, solenoid, 24 VDC to lock, 270-degree fixed head, 1200N holding force, (2) N.C. safety output(s), (1) N.C. monitoring output(s), thermoplastic body, 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AFEPMKR4FR3-024E>

Technical Specifications

Brand	Comepi
Item	Safety switch
Actuator Type	Tongue (key) interlock uniquely coded RFID
Lock Type	Solenoid, 24 VDC to lock
Head Type	270-degree fixed
Holding Force	1200N
Safety Output Type	(2) N.C.
Monitoring Output Type	(1) N.C.
Indicating Type	(3) status LEDs
Housing Size	40 x 198 x 50mm
Body Material	Thermoplastic
Head Material	Thermoplastic
IP Rating	IP65
Connection	8-pin M12 quick-disconnect

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AFEPMKR4FR3-024E.pdf>
See store item page for other formats.