

# AFR-4433-MD Cut Sheet



NITRA pneumatic filter-regulator, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), 20-130 psi adjustable range, manual drain, die-cast aluminum bowl, sight gauge. For use with Ax-44 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AFR-4433-MD>

## Technical Specifications

|                       |   |
|-----------------------|---|
| <b>Brand</b>          | NITRA   |
| <b>Item</b>           | Filter-regulator  |
| <b>Working Fluid</b>  | Air or inert gas  |
| <b>Inlet Port</b>     | 1/2in female NPT  |
| <b>Outlet Port</b>    | 1/2in female NPT  |
| <b>Pressure Range</b> | 20-130 psi adjustable   |
| <b>Drain Type</b>     | Manual  |
| <b>Bowl Material</b>  | Die-cast aluminum   |
| <b>Bowl Guard</b>     | No  |
| <b>Sight Gauge</b>    | Yes   |
| <b>For Use With</b>   | Ax-44 series air prep components  |
| <b>Includes</b>       | Integral pressure gauge, locking adjustment knob, replaceable 40 micron filter element and mounting bracket |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AFR-4433-MD.pdf>  
See store item page for other formats.