

AFR2-3233-AD Cut Sheet



NITRA pneumatic filter-regulator, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), 20-130 psi adjustable range, automatic drain, die-cast aluminum bowl, sight gauge. For use with Ax-32 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AFR2-3233-AD>

Technical Specifications

Brand	NITRA
Item	Filter-regulator
Working Fluid	Air or inert gas
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Pressure Range	20-130 psi adjustable
Drain Type	Automatic
Bowl Material	Die-cast aluminum
Bowl Guard	No
Sight Gauge	Yes
For Use With	Ax-32 series air prep components
Includes	Integral pressure gauge, locking adjustment knob and replaceable 40 micron filter element and mounting bracket

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AFR2-3233-AD.pdf>
See store item page for other formats.