

AFR2-3332-N Cut Sheet



NITRA pneumatic filter-regulator, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), 20-60 psi adjustable range, manual/semi-automatic drain, nylon bowl, bowl guard. For use with Ax-33 series air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AFR2-3332-N>

Technical Specifications

| | |
|-----------------------|--|
| Brand | NITRA |
| Item | Filter-regulator |
| Working Fluid | Air or inert gas |
| Inlet Port | 3/8in female NPT |
| Outlet Port | 3/8in female NPT |
| Pressure Range | 20-60 psi adjustable |
| Drain Type | Manual/semi-automatic |
| Bowl Material | Nylon |
| Bowl Guard | Yes |
| Sight Gauge | No |
| For Use With | Ax-33 series air prep components |
| Includes | Integral pressure gauge, locking adjustment knob and replaceable 40 micron filter element and mounting bracket |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/AFR2-3332-N.pdf>
See store item page for other formats.