

AGC25 Cut Sheet



Bussmann fuse, AGC series, small dimension, fast-acting, 25A, 32 VAC, glass tube. Package of 5. Supplemental, electronic protection applications. Manufacturer part number: AGC-25-R.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AGC25>

Technical Specifications

Brand	Bussmann
Item	Fuse
Series	AGC
Fuse Class	Small dimension
Curve Characteristics	Fast-acting
Amperage Rating	25A
Voltage Rating	32 VAC
Body Type	Glass tube
Size	1/4x1-1/4in or 6.3mm x 32mm
Quantity per Pack	5
Application	Supplemental, electronic protection applications
Manufacturer Part Number	AGC-25-R

Agency Approvals

UL Listed File #	E19180
UL Recognized File #	E19180
UL Hazardous File #	None
CE	None
CSA File #	227483
RoHS Status	No
EU REACH	View EU REACH document
Other	None