

AH1083C Cut Sheet



AttaBox Heartland SL series enclosure, NEMA 1/3R/4/4X/12, 10 x 8 x 3in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, smoked polycarbonate single-door, polycarbonate quick-release latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AH1083C>

Technical Specifications

Brand	AttaBox
Item	Enclosure
Series	Heartland SL
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/3R/4/4X/12
IP Rating	IP66
Nominal Enclosure Dimensions	10 x 8 x 3in (HxWxD)
Enclosure Height	11.41in
Enclosure Width	9.41in
Enclosure Depth	4.64in
Mounting	Wall

Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Polycarbonate
Color	Pantone 7541 C light gray
Cover Type	Smoked polycarbonate single-door
Latch Type	Polycarbonate quick-release latch
Number Of Latches	2
Padlockable	Yes
Keylocking	No
Includes	Mounting feet and hardware

Agency Approvals

UL Listed File #	E319779
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document