AH12104C Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

AttaBox Heartland SL series enclosure, NEMA 1/3R/4/4X/12, 12 x 10 x 4in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, smoked polycarbonate single-door, polycarbonate quick-release latch, molded hasp.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/AH12104C

Technical Specifications

Brand	AttaBox
Series	Heartland SL
Item	Enclosure
Subpanel	Purchase subpanel separately
NEMA Rating	1/3R/4/4X/12
IP Rating	IP66
Nominal Enclosure Height	12in
Nominal Enclosure Width	10in
Nominal Enclosure Depth	4in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No
Knockouts	No

Material	Polycarbonate
Color	Pantone 7541 C light gray
Cover Type	Smoked polycarbonate single-door
Hinge Type	External molded hinges
Number of Hinges Per Door	8
Latch Type	Polycarbonate quick-release latch
Number Of Latches	2
Padlockable	Yes
Padlock Attachment Type	Molded hasp
Keylocking	No
Shelf	No
Includes	Mounting feet and hardware

Agency Approvals

UL Listed File #	E319779
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/AH12104C.pdf
See store item page for other formats.