

AH14124CSS Cut Sheet



AttaBox Heartland SL series enclosure, NEMA 1/3R/4/4X/12, 14 x 12 x 4in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, smoked polycarbonate single-door, stainless steel quick-release latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AH14124CSS>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | AttaBox |
| Item | Enclosure |
| Series | Heartland SL |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 1/3R/4/4X/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 14 x 12 x 4in (HxWxD) |
| Enclosure Height | 15.40in |
| Enclosure Width | 13.40in |
| Enclosure Depth | 5.39in |
| Mounting | Wall |

| | |
|---------------------------------|-------------------------------------|
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Polycarbonate |
| Color | Pantone 7541 C light gray |
| Cover Type | Smoked polycarbonate single-door |
| Latch Type | Stainless steel quick-release latch |
| Number Of Latches | 2 |
| Shelf | No |
| Padlockable | Yes |
| Keylocking | No |
| Includes | Mounting feet and hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E319779 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/AH14124CSS.pdf>
See store item page for other formats.