

AH20164SS Cut Sheet



AttaBox Heartland SL series enclosure, NEMA 1/3R/4/4X/12, 20 x 16 x 4in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, single-door, stainless steel quick-release latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AH20164SS>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | AttaBox |
| Item | Enclosure |
| Series | Heartland SL |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 1/3R/4/4X/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 20 x 16 x 4in (HxWxD) |
| Enclosure Height | 21.41in |
| Enclosure Width | 17.41in |
| Enclosure Depth | 5.47in |
| Mounting | Wall |

| | |
|---------------------------------|-------------------------------------|
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Polycarbonate |
| Color | Pantone 7541 C light gray |
| Cover Type | Single-door |
| Latch Type | Stainless steel quick-release latch |
| Number Of Latches | 4 |
| Padlockable | Yes |
| Keylocking | No |
| Includes | Mounting feet and hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E319779 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |