

# AH884CSS Cut Sheet



AttaBox Heartland series enclosure, NEMA 1/3R/4/4X/12, 8 x 8 x 4in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, smoked polycarbonate single-door, stainless steel quick-release latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AH884CSS>

## Technical Specifications

<b>Brand</b>	AttaBox
<b>Item</b>	Enclosure
<b>Series</b>	Heartland
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>3-Piece Assembly</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	1/3R/4/4X/12
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	8 x 8 x 4in (HxWxD)
<b>Enclosure Height</b>	9.41in
<b>Enclosure Width</b>	9.41in
<b>Enclosure Depth</b>	5.36in
<b>Mounting</b>	Wall

<b>Integral Mounting Feet</b>	No
<b>Integral Mounting Flange</b>	No
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Bottom Gland Plate</b>	No
<b>Material</b>	Polycarbonate
<b>Color</b>	Pantone 7541 C light gray
<b>Cover Type</b>	Smoked polycarbonate single-door
<b>Latch Type</b>	Stainless steel quick-release latch
<b>Number Of Latches</b>	1
<b>Shelf</b>	No
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Includes</b>	Mounting feet and hardware

## Agency Approvals

<b>UL Listed File #</b>	E319779
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/AH884CSS.pdf>  
See store item page for other formats.