

AHF14126 Cut Sheet



AttaBox Heartland series enclosure, NEMA 1/3R/4/4X/12, 14 x 12 x 6in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, single-door, polycarbonate quick-release latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AHF14126>

Technical Specifications

| | | | |
|-------------------------------------|------------------------------|---------------------------------|-----------------------------------|
| Brand | AttaBox | Integral Mounting Feet | No |
| Item | Enclosure | Integral Mounting Flange | No |
| Series | Heartland | Dual Access | No |
| Subpanel | Purchase subpanel separately | Knockouts | No |
| Slope Top | No | Bottom Gland Plate | No |
| 3-Piece Assembly | No | Material | Polycarbonate |
| Vented | No | Color | Pantone 7541 C light gray |
| NEMA Rating | 1/3R/4/4X/12 | Cover Type | Single-door |
| IP Rating | IP66 | Latch Type | Polycarbonate quick-release latch |
| Nominal Enclosure Dimensions | 14 x 12 x 6in (HxWxD) | Number Of Latches | 2 |
| Enclosure Height | 15.40in | Padlockable | Yes |
| Enclosure Width | 13.40in | Keylocking | No |
| Enclosure Depth | 7.39in | Includes | Mounting flanges and hardware |
| Mounting | Wall | | |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E319779 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |