

# AHP2T11J02-024 Cut Sheet



AchieVe IEC limit switch, metal plunger, 90-degree adjustable head, (2) N.C. contact(s), snap action, solenoid reset, 20-22mm hole spacing, plastic, (2) PG11 and (1) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AHP2T11J02-024>

## Technical Specifications

Brand	AchieVe	Body Width	30.3mm
Item	Limit switch	Mounting Hole Spacing	20-22mm
Switch Type	IEC	Material	Plastic
Actuator Type	Metal plunger	IP Rating	IP65
Head Type	90-degree adjustable	Operating Temperature	-25 to 70 deg C
Contact Type	(2) N.C.	Connection	(2) PG11 and (1) 1/2in NPT cable entries
Action	Snap action	Halogen Free	No
Reset	Solenoid		

## Agency Approvals

UL Listed File #	NKCR.E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/AHP2T11J02-024.pdf>  
See store item page for other formats.